

# Hoshizaki America, Inc.

## Stackable Crescent Cuber

### Models

KMH-2000SVWH/3

KMH-2000SRH/3



“A Superior Degree  
of Reliability”

[www.hoshizaki.com](http://www.hoshizaki.com)

## PARTS LIST



Number: 71316  
Issued: 5-3-2011  
Revised: 2-5-2016

## CONTENTS

|                                                |    |
|------------------------------------------------|----|
| Auxiliary Codes.....                           | 3  |
| Note About Ordering Parts .....                | 3  |
| A. Main Assembly & Refrigeration Circuit ..... | 4  |
| KMH-2000SWH/3.....                             | 4  |
| KMH-2000SRH/3 .....                            | 7  |
| B. Water Circuit .....                         | 10 |
| C. Control Box Assembly .....                  | 13 |
| D. Accesories & Labels .....                   | 14 |

## Auxiliary Codes

### KMH-2000SWH

V-0 January 2010  
V-1 November 2010  
A-0 February 2011  
C-0 July 2013  
E-1 October 2015

### KMH-2000SRH

V-0 April 2010  
A-0 April 2011  
A-1 September 2011  
B-0 September 2012  
C-0 May 2013  
D-0 January 2014  
E-1 November 2015  
F-0 January 2016

### KMH-2000SWH3

V-0 January 2010  
V-1 December 2010  
A-0 January 2011  
B-0 April 2012  
C-0 July 2013  
D-1 March 2014  
E-0 February 2015  
E-1 October 2015  
F-0 February 2016

### KMH-2000SRH3

V-0 April 2010  
A-0 January 2011  
A-1 September 2011  
B-0 March 2012  
C-0 April 2013  
D-0 January 2014  
E-0 January 2015  
E-1 October 2015  
F-0 February 2016


## Auxiliary Code Breakdown

The auxiliary code is the first two characters in the serial number. The first character indicates the year. Years progress or regress in alphabetical order. The series runs from "A" through "V" and the letters "I" and "O" are skipped. The second character indicates significant part changes within a year. Base is "0" and this number advances for each change. In cases where there is a letter in parentheses, this designates the month. This is the last character in the serial number. The series runs from "(A)" through "(M)" and the letter "(I)" is skipped. This designation is only included when identifying a parts change within an auxiliary code.

## Note About Ordering Parts

Most assemblies cannot be ordered as complete units; parts in the assemblies generally must be ordered separately.


# **A. Main Assembly & Refrigeration Circuit** **KMH-2000SWH/3** V-0 to F-0



| Title: A. Main Assembly & Refrigeration Circuit     Model: KMH-2000SWH/3 |                                                  |                                      |             |                 |            |            |  |  |  |  |  |  |
|--------------------------------------------------------------------------|--------------------------------------------------|--------------------------------------|-------------|-----------------|------------|------------|--|--|--|--|--|--|
| Index No.                                                                | Description                                      | Material or Model Number             | Part Number | Required Number |            |            |  |  |  |  |  |  |
|                                                                          |                                                  |                                      |             | V-0 to A-0      | A-1 to D-0 | D-1 to F-0 |  |  |  |  |  |  |
| Main Assembly                                                            |                                                  |                                      |             |                 |            |            |  |  |  |  |  |  |
| 1                                                                        | Front Panel                                      |                                      | 2A5369-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 2                                                                        | Top Panel                                        |                                      | 2A5368-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 3                                                                        | Right Side Panel                                 |                                      | 2A5360G01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 4                                                                        | Front Insulation                                 |                                      | 326041G01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 4a                                                                       | Thumbscrew                                       |                                      | 415949G12   | 1               | 1          | 1          |  |  |  |  |  |  |
| 5                                                                        | Top Insulation                                   |                                      | 324216G01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 6                                                                        | Spacer                                           |                                      | 324321-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 7                                                                        | Control Box Cover A                              |                                      | 3A5625-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 8                                                                        | Control Box Cover B                              |                                      | 3A5626-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 9                                                                        | Junction Box Cover                               |                                      | 433410-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 10                                                                       | Bin Control Bulb Holder C                        |                                      | 216340G01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 11                                                                       | Bin Control Bulb Holder C                        | Z Bracket                            | 325845G01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 12                                                                       | Bin Control Bulb Holder E                        |                                      | 439725-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 13                                                                       | Bin Control Bulb Holder F                        |                                      | 328743-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 13a                                                                      | Thumbscrew                                       |                                      | 415949G12   | 2               | 2          | 2          |  |  |  |  |  |  |
| 14                                                                       | Bin Control Bulb Holder G                        |                                      | 439726-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 15                                                                       | Spacer                                           |                                      | 439727-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 16                                                                       | Capillary Ring                                   |                                      | 425307-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 17                                                                       | Thermostat Extension Bracket                     |                                      | 3A0408-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 18                                                                       | Bulb Holder                                      |                                      | 3A3903-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 19                                                                       | Silicone Hose                                    | L=285 mm                             | 773013812   | 1               | 1          | 1          |  |  |  |  |  |  |
| 20                                                                       | Start Capacitor                                  | KMH-2000SWH<br>189-227MFD,<br>330VAC | 3A0076-12   | 1               | 1          | 1          |  |  |  |  |  |  |
| 21                                                                       | Run Capacitor                                    | KMH-2000SWH<br>35MFD,<br>440VAC      | 3A2005-12   | 1               | 1          | 1          |  |  |  |  |  |  |
| 22                                                                       | Capacitor Box Cover                              | KMH-2000SWH                          | 326125-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 23                                                                       | Start Relay                                      | KMH-2000SWH                          | 4A1107-09   | 1               | 1          | 1          |  |  |  |  |  |  |
| 24                                                                       | Transformer                                      | KMH-2000SWH3                         | 4A0817-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 25                                                                       | Voltage Tap Switch                               | KMH-2000SWH3                         | 4A1477-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| Refrigeration Circuit                                                    |                                                  |                                      |             |                 |            |            |  |  |  |  |  |  |
| 26                                                                       | Compressor                                       | KMH-2000SWH                          | 4A4581-02   | 1               | -          |            |  |  |  |  |  |  |
|                                                                          |                                                  |                                      | 4A4581-01   |                 | 1          | 1          |  |  |  |  |  |  |
|                                                                          |                                                  | KMH-2000SWH3                         | 4A4582-02   | 1               | -          |            |  |  |  |  |  |  |
|                                                                          |                                                  |                                      | 4A4582-01   |                 | 1          | 1          |  |  |  |  |  |  |
| 27                                                                       | Condenser                                        | HS-0164                              | 2A2359G05   | 1               | 1          | -          |  |  |  |  |  |  |
|                                                                          |                                                  |                                      | 3A7324-01   |                 |            | 1          |  |  |  |  |  |  |
| 28                                                                       | Evaporator Bank<br>(each bank includes 3 plates) | HS-008                               | 2A0416G01   | 2               | 2          | 2          |  |  |  |  |  |  |
| 29                                                                       | Separator Hook                                   |                                      | 324152-01   | 8               | 8          | 8          |  |  |  |  |  |  |
| 30                                                                       | ThermostaticExpansion Valve                      |                                      | 4A1414-01   | 3               | 3          | 3          |  |  |  |  |  |  |
| 31                                                                       | Thermostatic Expansion Valve<br>Cover            |                                      | 3A0944-01   | 3               | 3          | 3          |  |  |  |  |  |  |
| 32                                                                       | Thermostatic Expansion Valve<br>Bulb Holder      |                                      | 3A0107-01   | 3               | 3          | 3          |  |  |  |  |  |  |
| 33                                                                       | Clamp                                            |                                      | 443461-02   | 3               | 3          | 3          |  |  |  |  |  |  |

| Title: A. Main Assembly & Refrigeration Circuit    Model: KMH-2000SWH/3 |                        |                          |             |                 |            |            |  |  |  |  |  |  |
|-------------------------------------------------------------------------|------------------------|--------------------------|-------------|-----------------|------------|------------|--|--|--|--|--|--|
| Index No.                                                               | Description            | Material or Model Number | Part Number | Required Number |            |            |  |  |  |  |  |  |
|                                                                         |                        |                          |             | V-0 to A-0      | A-1 to D-0 | D-1 to F-0 |  |  |  |  |  |  |
| 34                                                                      | Hot Gas Valve Body     |                          | 4A3978-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 35                                                                      | Liquid Line Valve Body |                          | 4A3276-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 36                                                                      | Valve Coil             |                          | 4A3277-01   | 2               | 2          | 2          |  |  |  |  |  |  |
| 37                                                                      | Check Valve            |                          | 4A1373-01   | 3               | 3          | 3          |  |  |  |  |  |  |
| 38                                                                      | Strainer               |                          | 441569-02   | 1               | 1          | 1          |  |  |  |  |  |  |
| 39                                                                      | High-Pressure Switch   |                          | 463180-05   | 1               | 1          | 1          |  |  |  |  |  |  |
| 40                                                                      | Thermistor             |                          | 429006-03   | 1               | 1          | 1          |  |  |  |  |  |  |
| 41                                                                      | Thermistor Holder      |                          | 438247-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 42                                                                      | Drier                  |                          | 4A2663-01   | 1               | 1          | 1          |  |  |  |  |  |  |
| 43                                                                      | Water Regulating Valve |                          | 4A0911-07   | 1               | 1          | 1          |  |  |  |  |  |  |


# **A. Main Assembly & Refrigeration Circuit** **KMH-2000SRH/3** V-0 to F-0




| Title: A. Main Assembly & Refrigeration Circuit    Model: KMH-2000SRH/3 |                                                                                               |                                      |             |                 |            |  |  |  |  |  |  |  |
|-------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|--------------------------------------|-------------|-----------------|------------|--|--|--|--|--|--|--|
| Index No.                                                               | Description                                                                                   | Material or Model Number             | Part Number | Required Number |            |  |  |  |  |  |  |  |
|                                                                         |                                                                                               |                                      |             | V-0 to A-0      | A-1 to F-0 |  |  |  |  |  |  |  |
| Main Assembly                                                           |                                                                                               |                                      |             |                 |            |  |  |  |  |  |  |  |
| 1                                                                       | Front Panel                                                                                   |                                      | 2A5369-01   | 1               | 1          |  |  |  |  |  |  |  |
| 2                                                                       | Top Panel                                                                                     |                                      | 2A5368-01   | 1               | 1          |  |  |  |  |  |  |  |
| 3                                                                       | Right Side Panel                                                                              |                                      | 2A5360G01   | 1               | 1          |  |  |  |  |  |  |  |
| 4                                                                       | Front Insulation                                                                              |                                      | 326041G01   | 1               | 1          |  |  |  |  |  |  |  |
| 4a                                                                      | Thumbscrew                                                                                    |                                      | 415949G12   | 1               | 1          |  |  |  |  |  |  |  |
| 5                                                                       | Top Insulation                                                                                |                                      | 324216G01   | 1               | 1          |  |  |  |  |  |  |  |
| 6                                                                       | Spacer                                                                                        |                                      | 324321-01   | 1               | 1          |  |  |  |  |  |  |  |
| 7                                                                       | Contol Box Cover A                                                                            |                                      | 3A5625-01   | 1               | 1          |  |  |  |  |  |  |  |
| 8                                                                       | Contol Box Cover B                                                                            |                                      | 3A5626-01   | 1               | 1          |  |  |  |  |  |  |  |
| 9                                                                       | Junction Box Cover                                                                            |                                      | 433410-01   | 2               | 2          |  |  |  |  |  |  |  |
| 10                                                                      | Bin Control Bulb Holder C                                                                     |                                      | 216340G01   | 1               | 1          |  |  |  |  |  |  |  |
| 11                                                                      | Bin Control Bulb Holder C                                                                     | Z Bracket                            | 325845G01   | 1               | 1          |  |  |  |  |  |  |  |
| 12                                                                      | Bin Control Bulb Holder E                                                                     |                                      | 439725-01   | 1               | 1          |  |  |  |  |  |  |  |
| 13                                                                      | Bin Control Bulb Holder F                                                                     |                                      | 328743-01   | 1               | 1          |  |  |  |  |  |  |  |
| 13a                                                                     | Thumbscrew                                                                                    |                                      | 415949G12   | 2               | 2          |  |  |  |  |  |  |  |
| 14                                                                      | Bin Control Bulb Holder G                                                                     |                                      | 439726-01   | 1               | 1          |  |  |  |  |  |  |  |
| 15                                                                      | Spacer                                                                                        |                                      | 439727-01   | 1               | 1          |  |  |  |  |  |  |  |
| 16                                                                      | Capillary Ring                                                                                |                                      | 425307-01   | 1               | 1          |  |  |  |  |  |  |  |
| 17                                                                      | Thermostat Extension Bracket                                                                  |                                      | 3A0408-01   | 1               | 1          |  |  |  |  |  |  |  |
| 18                                                                      | Bulb Holder                                                                                   |                                      | 3A3903-01   | 1               | 1          |  |  |  |  |  |  |  |
| 19                                                                      | Silicone Hose                                                                                 | L=285 mm                             | 773013812   | 1               | 1          |  |  |  |  |  |  |  |
| 20                                                                      | Start Capacitor                                                                               | KMH-2000SRH<br>189-227MFD,<br>330VAC | 3A0076-12   | 1               | 1          |  |  |  |  |  |  |  |
| 21                                                                      | Run Capacitor                                                                                 | KMH-2000SRH<br>35MFD,<br>440VAC      | 3A2005-12   | 1               | 1          |  |  |  |  |  |  |  |
| 22                                                                      | Capacitor Box Cover                                                                           |                                      | 326125-01   | 1               | 1          |  |  |  |  |  |  |  |
| 23                                                                      | Start Relay                                                                                   | KMH-2000SRH                          | 4A1107-09   | 1               | 1          |  |  |  |  |  |  |  |
| 24                                                                      | Transformer                                                                                   | KMH-2000SRH3                         | 4A0817-01   | 1               | 1          |  |  |  |  |  |  |  |
| 25                                                                      | Voltage Tap Switch                                                                            | KMH-2000SRH3                         | 4A1477-01   | 1               | 1          |  |  |  |  |  |  |  |
| Refrigeration Circuit                                                   |                                                                                               |                                      |             |                 |            |  |  |  |  |  |  |  |
| 26                                                                      | Compressor<br>(Note: Aux. Code A-1 and later<br>utilize external crankcase<br>heater item 27) | KMH-2000SRH                          | 4A4581-02   | 1               | -          |  |  |  |  |  |  |  |
|                                                                         |                                                                                               |                                      | 4A4581-01   |                 | 1          |  |  |  |  |  |  |  |
|                                                                         |                                                                                               | KMH-2000SRH3                         | 4A4582-02   | 1               | -          |  |  |  |  |  |  |  |
|                                                                         |                                                                                               |                                      | 4A4582-01   |                 | 1          |  |  |  |  |  |  |  |
| 27                                                                      | Crankcase Heater                                                                              |                                      | 434186-01   |                 | 1          |  |  |  |  |  |  |  |
| 28                                                                      | Receiver                                                                                      |                                      | 438209-01   | 1               | 1          |  |  |  |  |  |  |  |
| 28a                                                                     | Hex Head Bolt w/Washer                                                                        | 5x10                                 | 7B0130510   | 3               | 3          |  |  |  |  |  |  |  |
| 29                                                                      | Evaporator Bank<br>(each bank includes 3 plates)                                              | HS-008                               | 2A0416G01   | 2               | 2          |  |  |  |  |  |  |  |
| 30                                                                      | Separator Hook                                                                                |                                      | 324152-01   | 8               | 8          |  |  |  |  |  |  |  |
| 31                                                                      | Thermostatic Expansion Valve                                                                  |                                      | 4A1414-01   | 3               | 3          |  |  |  |  |  |  |  |
| 32                                                                      | Thermostatic Expansion Valve<br>Cover                                                         |                                      | 3A0944-01   | 3               | 3          |  |  |  |  |  |  |  |
| 33                                                                      | Thermostatic Expansion Valve<br>Bulb Holder                                                   |                                      | 3A0107-01   | 3               | 3          |  |  |  |  |  |  |  |

| Title: A. Main Assembly & Refrigeration Circuit    Model: KMH-2000SRH/3 |                        |                          |             |                 |            |  |  |  |  |  |  |  |
|-------------------------------------------------------------------------|------------------------|--------------------------|-------------|-----------------|------------|--|--|--|--|--|--|--|
| Index No.                                                               | Description            | Material or Model Number | Part Number | Required Number |            |  |  |  |  |  |  |  |
|                                                                         |                        |                          |             | V-0 to A-0      | A-1 to F-0 |  |  |  |  |  |  |  |
| 34                                                                      | Clamp                  |                          | 443461-02   | 3               | 3          |  |  |  |  |  |  |  |
| 35                                                                      | Hot Gas Valve Body     |                          | 4A3978-01   | 1               | 1          |  |  |  |  |  |  |  |
| 36                                                                      | Liquid Line Valve Body |                          | 4A3276-01   | 1               | 1          |  |  |  |  |  |  |  |
| 37                                                                      | Valve Coil             |                          | 4A3277-01   | 2               | 2          |  |  |  |  |  |  |  |
| 38                                                                      | Check Valve            |                          | 4A1373-01   | 3               | 3          |  |  |  |  |  |  |  |
| 39                                                                      | Strainer               |                          | 441569-02   | 1               | 1          |  |  |  |  |  |  |  |
| 40                                                                      | High-Pressure Switch   |                          | 463180-04   | 1               | 1          |  |  |  |  |  |  |  |
| 41                                                                      | Thermistor             |                          | 429006-03   | 1               | 1          |  |  |  |  |  |  |  |
| 42                                                                      | Thermistor Holder      |                          | 438247-01   | 1               | 1          |  |  |  |  |  |  |  |
| 43                                                                      | Drier                  |                          | 4A2663-01   | 1               | 1          |  |  |  |  |  |  |  |

**B. Water Circuit**  
**KMH-2000S\_H/3**  
 V-0 to F-0



**Pump Motor Assembly**




**Title: B. Water Circuit    Model: KMH-2000S\_H/3**

| Index No. | Description                                       | Material or Model Number | Part Number | Required Number |     |            |  |  |  |  |  |
|-----------|---------------------------------------------------|--------------------------|-------------|-----------------|-----|------------|--|--|--|--|--|
|           |                                                   |                          |             | V-0             | V-1 | A-0 to F-0 |  |  |  |  |  |
| 1         | Pump Motor Assembly (includes items 2 through 8b) | S-0730                   | 215692A03   | 1               | 1   | 1          |  |  |  |  |  |
| 2         | Pump Flange                                       |                          | 215662-01   | 1               | 1   | 1          |  |  |  |  |  |
| 2a        | Tooth Washer                                      | M6, SS                   | 7R22-0600   | 2               | 2   | 2          |  |  |  |  |  |
| 2b        | Hex Head Bolt                                     | 6x40, SS                 | 7B02-0640   | 4               | 4   | 4          |  |  |  |  |  |
| 2c        | Flat Washer                                       | M6, SS                   | 7W22-0600   | 4               | 4   | 4          |  |  |  |  |  |
| 2d        | Split Lock Washer                                 | M6, SS                   | 7L22-0600   | 4               | 4   | 4          |  |  |  |  |  |
| 2e        | Hex Nut                                           | M6, SS                   | 7N12-0600   | 4               | 4   | 4          |  |  |  |  |  |
| 3         | Pump Motor Bracket                                |                          | 323904-01   | 1               | 1   | 1          |  |  |  |  |  |
| 4         | Mechanical Seal                                   |                          | 4A3820-01   | 1               | 1   | 1          |  |  |  |  |  |
| 5         | Packing                                           |                          | 428547-01   | 1               | 1   | 1          |  |  |  |  |  |
| 6         | Impeller                                          |                          | 436584-01   | 1               | 1   | 1          |  |  |  |  |  |
| 7         | Pin                                               |                          | 4A0648-01   | 1               | 1   | 1          |  |  |  |  |  |
| 8         | Pump Housing                                      |                          | 213687-01   | 1               | 1   | 1          |  |  |  |  |  |
| 8a        | Hex Head Bolt                                     | 4x55, SS                 | 7B02-0455   | 4               | 4   | 4          |  |  |  |  |  |
| 8b        | Hex Flange Nut                                    | 4, SS                    | 7J02-0400   | 4               | 4   | 4          |  |  |  |  |  |
| 9         | Water Supply Pipe                                 |                          | 3A5631G01   | 1               | 1   | 1          |  |  |  |  |  |
| 10        | Rubber Gasket                                     |                          | 413854-03   | 1               | 1   | 1          |  |  |  |  |  |
| 11        | Inlet Water Valve                                 |                          | 4A1176-04   | 1               | -   |            |  |  |  |  |  |
|           |                                                   |                          | 4A5251-04   |                 | 1   | 1          |  |  |  |  |  |
| 12        | Distributor Hose A                                |                          | 325738-01   | 1               | 1   | 1          |  |  |  |  |  |
| 13        | Distributor Hose B                                |                          | 325738-02   | 1               | 1   | 1          |  |  |  |  |  |
| 14        | Distributor Hose C                                |                          | 325739-01   | 2               | 2   | 2          |  |  |  |  |  |
| 15        | Joint Pipe                                        |                          | 439297-01   | 1               | 1   | 1          |  |  |  |  |  |
| 16        | Spray Tube                                        |                          | 437049G01   | 6               | 6   | 6          |  |  |  |  |  |
| 17        | Spray Guide                                       |                          | 208586-01   | 18              | 18  | 18         |  |  |  |  |  |
| 18        | Separator A                                       |                          | 215046-01   | 2               | 2   | 2          |  |  |  |  |  |
| 19        | Separator B                                       |                          | 2A0100-01   | 2               | 2   | 2          |  |  |  |  |  |
| 20        | Cube Guide                                        |                          | 214243-01   | 2               | 2   | 2          |  |  |  |  |  |
| 21        | Hose A                                            |                          | 435091-01   | 1               | 1   | 1          |  |  |  |  |  |
| 22        | Hose B                                            |                          | 325867-01   | 1               | 1   | 1          |  |  |  |  |  |
| 23        | Distributor A                                     |                          | 439266-01   | 1               | 1   | 1          |  |  |  |  |  |
| 24        | Distributor B                                     |                          | 439239-01   | 1               | 1   | 1          |  |  |  |  |  |
| 25        | Distributor C                                     |                          | 439238-01   | 1               | 1   | 1          |  |  |  |  |  |
| 26        | Drain Valve Housing                               |                          | 323613-01   | 1               | 1   | 1          |  |  |  |  |  |
| 27        | Drain Valve Spring                                |                          | 322110-01   | 1               | 1   | 1          |  |  |  |  |  |
| 28        | Drain Valve Seat                                  |                          | 433705-01   | 1               | 1   | 1          |  |  |  |  |  |
| 29        | Overflow Cap                                      |                          | 325866-01   | 1               | 1   | 1          |  |  |  |  |  |
| 30        | Overflow Joint                                    |                          | 323923-02   | 1               | 1   | 1          |  |  |  |  |  |
| 31        | Float Switch Connector                            |                          | 426799-04   | 1               | 1   | 1          |  |  |  |  |  |
| 32        | Float Switch                                      |                          | 4A3624-01   | 1               | 1   | 1          |  |  |  |  |  |
| 33        | Overflow Joint O-Ring                             |                          | 7611-P018   | 1               | 1   | 1          |  |  |  |  |  |
| 34        | Drain Valve O-Ring                                |                          | 7611-G035   | 1               | 1   | 1          |  |  |  |  |  |
| 35        | Drain Hose                                        |                          | 325869-01   | 1               | 1   | 1          |  |  |  |  |  |
| 36        | Drain Plug                                        |                          | 309246-01   | 1               | 1   | 1          |  |  |  |  |  |
| 37        | Drain Plug O-Ring                                 |                          | 7611-P015   | 1               | 1   | 1          |  |  |  |  |  |

| Title: B. Water Circuit    Model: KMH-2000S_H/3 |                             |                          |             |                 |     |                                   |  |  |  |  |  |
|-------------------------------------------------|-----------------------------|--------------------------|-------------|-----------------|-----|-----------------------------------|--|--|--|--|--|
| Index No.                                       | Description                 | Material or Model Number | Part Number | Required Number |     |                                   |  |  |  |  |  |
|                                                 |                             |                          |             | V-0             | V-1 | A-0 to F-0                        |  |  |  |  |  |
| 38                                              | Joint Hose                  |                          | 439309-01   | 1               | 1   | 1                                 |  |  |  |  |  |
| 39                                              | Bypass Hose                 |                          | 439237-02   | 1               | 1   | 1                                 |  |  |  |  |  |
| 40                                              | Cleaning Valve Ball Valve   |                          | 439293-01   | 1               | 1   | 1                                 |  |  |  |  |  |
| 41                                              | Cleaning Valve Male Adaptor |                          | 325826-01   | 2               | 2   | 2                                 |  |  |  |  |  |
| 42                                              | Cleaning Valve O-Ring       |                          | 7611-P018   | 2               | 2   | Replaced with thread sealant tape |  |  |  |  |  |
| 43                                              | Cleaning Valve Microswitch  |                          | 4A2546-01   | 1               | 1   | 1                                 |  |  |  |  |  |
| 44                                              | Cleaning Valve Handle       |                          | 215383-01   | 1               | 1   | 1                                 |  |  |  |  |  |
| 45                                              | Silicone Hose               | L=190 mm                 | 773013812   | 1               | 1   | 1                                 |  |  |  |  |  |
| 46                                              | Silicone Hose               | L=430 mm                 | 773013896   | 1               | 1   | 1                                 |  |  |  |  |  |
| 47                                              | Vinyl Hose                  | L=40 mm                  | 7716-1216   | 1               | 1   | 1                                 |  |  |  |  |  |
| 48                                              | Vinyl Hose                  | L=550 mm                 | 7716-2732   | 1               | 1   | 1                                 |  |  |  |  |  |
| 49                                              | Vinyl Hose                  | L=230 mm                 | 7716-2732   | 1               | 1   | 1                                 |  |  |  |  |  |
| <b>Hose Clamps</b>                              |                             |                          |             |                 |     |                                   |  |  |  |  |  |
|                                                 | Hose Clamp                  | 25 mm, SS                | 427443-03   | 9               | 9   | 9                                 |  |  |  |  |  |
|                                                 | Hose Clamp                  | 13.5 mm, SS              | 427443-07   | 6               | 6   | 6                                 |  |  |  |  |  |
|                                                 | Hose Clamp                  | 32 mm, SS                | 427443-09   | 6               | 6   | 6                                 |  |  |  |  |  |

**C. Control Box Assembly**  
**KMH-2000S\_H/3**  
V-0 to F-0



| Title: C. Control Box Assembly    Model: KMH-2000S_H/3 |                        |                          |             |                 |                |         |  |  |  |  |  |
|--------------------------------------------------------|------------------------|--------------------------|-------------|-----------------|----------------|---------|--|--|--|--|--|
| Index No.                                              | Description            | Material or Model Number | Part Number | Required Number |                |         |  |  |  |  |  |
|                                                        |                        |                          |             | V-0 to B-0 (C)  | B-0 (D) to E-0 | E-1 F-0 |  |  |  |  |  |
| 1                                                      | Magnetic Contactor     | KMH-2000SWH/3            | 4A0794-02   | 1               | 1              | 1       |  |  |  |  |  |
|                                                        |                        | KMH-2000SRH/3            | 4A0794-01   | 1               | 1              | 1       |  |  |  |  |  |
| 2                                                      | Pump Motor Capacitor   | 10MFD, 250VAC            | 443192-01   | 1               | 1              | 1       |  |  |  |  |  |
| 3                                                      | Control Transformer    |                          | 3A0172-01   | 1               | 1              | 1       |  |  |  |  |  |
| 4                                                      | "E" Control Board      |                          | 2A1410-01   | 1               | 1              | -       |  |  |  |  |  |
|                                                        | "G" Control Board      |                          | 2A3792-01   |                 |                | 1       |  |  |  |  |  |
| 4a                                                     | Control Board Support  |                          | 4A0336-03   | 4               | 4              | 4       |  |  |  |  |  |
| 5                                                      | Bin Control Thermostat |                          | 4A2879-02   | 1               | 1              | 1       |  |  |  |  |  |
| 6                                                      | Control Switch         |                          | 443119-01   | 1               | 1              | 1       |  |  |  |  |  |
| 7                                                      | Fuse Holder            | KMH-2000SWH/3            | 4A3449-01   | 1               | -              |         |  |  |  |  |  |
|                                                        |                        |                          | 4A5443-01   |                 | 1              | 1       |  |  |  |  |  |
|                                                        |                        | KMH-2000SRH/3            | 4A3449-01   | 1               | -              |         |  |  |  |  |  |
|                                                        |                        |                          | 4A5443-01   |                 | 1              | 1       |  |  |  |  |  |
| 8                                                      | Fuse                   | AGC-10A, 250VAC          | 4A0893-07   | 1               | 1              | 1       |  |  |  |  |  |
| 9                                                      | Jumper Connector       |                          | 4A4883G01   |                 |                | 1       |  |  |  |  |  |

## D. Accesories & Labels

### KMH-2000S\_H/3

V-0 to F-0

| Title: D. Accesories & Labels    Model: KMH-2000S_H/3 |                 |                          |             |                 |  |  |  |  |  |  |  |  |
|-------------------------------------------------------|-----------------|--------------------------|-------------|-----------------|--|--|--|--|--|--|--|--|
| Index No.                                             | Description     | Material or Model Number | Part Number | Required Number |  |  |  |  |  |  |  |  |
|                                                       |                 |                          |             | V-0 to F-0      |  |  |  |  |  |  |  |  |
| 1                                                     | Universal Brace |                          | 4A0363-01   | 2               |  |  |  |  |  |  |  |  |
| 1a                                                    | Hex Bolt        | 5x12, SS                 | 7B02-0512   | 2               |  |  |  |  |  |  |  |  |
| 2                                                     | Penguin Label   |                          | 4A0526-01   | 1               |  |  |  |  |  |  |  |  |